

PDA200E 200m2 Waiting room loop kit (PDA200E amplifier; APL outreach plate; 6m Belden cable) Part No. AKR1



Overview

Includes a PDA200E hearingloop amplifier and APL line level audio inputplate (for connecting to a paging system) and 6m of Belden cable.

Ideal for creatinga high quality hearingloop system for a waiting room.

Wall-mountable PDA200E amplifier capable of driving a perimeter loop of up to 200m2.

Internal drive, level and metal compensation controls.

Two balanced / unbalanced line level inputs.

One microphone input with 12V phantom power for electret microphones.

Full compatibility with the Outreach plate audio input extension system.

Fully compliant withBS EN 60118-4 when correctly installed.

Loop cable not included-use our LOOP2W1mm2 cable or download our AFILS loop calculator from our Software & Apps page formore precise recommendations.

Technical Specifications	
Туре	Wall mounting. Requires fixed Mains wiring.
Coverage	200m2 approx.
Mains supply	230V 50/60Hz.
Auxiliary inputs	1 Microphone and 2 x Line/Outreach screw connectors (on PDA200E).
Indicators	Input level; loop current meter (peak 3, 2, 1); compression; power on.
Controls	Input level; loop drive, metal compensation.
Product dimensions (mm)	W 271 x H 200 x D 77mm (amplifier only).
Construction & finish	White painted steel (PDA200E); plastic (APL).
IP Rating	IP20.
Weight	2.9 kg (amplifier only).

(LPCB) 💆

ISCE The Performed Sound and 

T 01942 322744 E sales@c-tec.co.uk

F 01942 829867 **W** www.c-tec.com

C-TEC, Challenge Way, Martland Park, Wigan, WN5 0LD United Kingdom



Operating conditions/temperature Kit contents -5°C to +40°C. Max relative humidity: 95%.

PDA200E 200m2 hearing loop amplifier; APL line level audio input plate; 1 x 6m Belden cable; Loop Fitted sticker. Loop cable IS NOT included.



 T
 01942 322744
 E
 sales@c-tec.co.uk

 F
 01942 829867
 W
 www.c-tec.com



